


# NA184N90, Substation - Copper Terminal

By Burndy  
Catalog # NA184N90

Substation Connectors.



## Application

Substation

## General

Catalog Number	NA184N90
Clamping Element Design	Body and Cap
Connector Type	Terminal
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	3.12 x 3 - 4 holes
Physical Attribute - Pad Orientation	90 Degree
Plated	N
Plating Type	Unplated
UPC	781810077276
UPC 12 Digit	7818100772766

## Dimensions

Dimension - B Length inch	2.69 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	3.44 in
Dimension - Height mm	87.4 mm
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	157 mm
Dimension - Length Overall inch	6.19 in
Dimension - N inch	0.62 in

Dimension - Pad Width inch	3.12 in
Dimension - Width inch	4.62 in
Dimension - Width mm	117 mm
Physical Attribute - Tongue Angle	90 Degree

## Conductor Related

Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	2 IPS
Conductor - Copper Tube Std Size Range	2 IPS
Conductor Type	<ul style="list-style-type: none"> <li>• CU Tube Std-Size</li> <li>• CU Tube EH-Size</li> </ul>
Number of Conductors	1

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	4
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD021664-01](#)
- [Specifications - NA184N90](#)