

# NA19A2N, Substation - Aluminum Bolted Terminal

By Burndy  
Catalog # [NA19A2N](#)



Substation Connectors.

## Application

Substation

## General

Catalog Number	NA19A2N
Clamping Element Design	Body and Cap
Connector Type	Terminal
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	3.25 x 3 - 2 holes
Plated	N
Plating Type	Unplated
UPC	781810252482
UPC 12 Digit	7818102524822

## Dimensions

Dimension - B Length inch	4.50 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - G inch	2.19 in
Dimension - Height inch	4.97 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	197 mm
Dimension - Length Overall inch	7.75 in
Dimension - N inch	0.63 in

Dimension - Pad Width inch	3.25 in
Dimension - Width inch	5.00 in
Dimension - Width mm	127 mm

## Conductor Related

Conductor - AL Tube Std Size	2 1/2 IPS
Conductor - AL Tube Std Size Range	2 1/2 IPS
Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	2 1/2 IPS IPS
Conductor - Copper Tube Std Size Range	2 1/2 IPS IPS
Conductor Type	<ul style="list-style-type: none"> <li>• AL Tube Std-Size</li> <li>• CU Tube Std-Size</li> </ul>
Number of Conductors	1

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SA038849-01](#)
- [Specifications - NA19A2N](#)