


NA194N, Substation - Copper Terminal, 2-1/2" Cu Pipe, 4-Hole NEMA

By Burndy
Catalog # NA194N



Copper Bolted Terminal, Tube to Flat, 2 1/2" Cu Pipe, 4 Pad Holes , 230 kV.

Application

Substation

General

Catalog Number	NA194N
Clamping Element Design	Body and Cap
Connector Type	Terminal
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	3.75 x 3 - 4 holes
Plated	N
Plating Type	Unplated
UPC	781810002506
UPC 12 Digit	7818100025066

Dimensions

Dimension - B Length inch	2.69 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	3-3/4
Dimension - Height inch	3.69 in
Dimension - Height mm	93.7 mm
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	151 mm
Dimension - Length Overall inch	5.94 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	3.75 in
Dimension - Width inch	5.25 in
Dimension - Width mm	133 mm

Conductor Related

Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube EH Size	2 1/2 IPS
Conductor - Copper Tube EH Size Range	2 1/2 IPS
Conductor - Copper Tube Std Size	2 1/2 IPS
Conductor - Copper Tube Std Size Range	2 1/2 IPS
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Size • CU Tube EH-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_NA132N_LineArt](#)
- [Sales Drawings - sa006759-01](#)
- [Specifications - NA194N](#)