

NA19A4NCG4, Substation - Aluminum Bolted Terminal

By Burndy
Catalog # [NA19A4NCG4](#)



Substation Connectors.

Application

Substation

General

Catalog Number	NA19A4NCG4
Clamping Element Design	Body and Cap
Connector Type	Terminal
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	4 holes
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
UPC	621945131293
UPC 12 Digit	6219451312933

Dimensions

Dimension - B Length inch	4.50 in
Dimension - D inch	3.50 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - G inch	2.19 in
Dimension - Height inch	4.97 in
Dimension - Height mm	126.2 mm
Dimension - L Length Overall mm	197 mm
Dimension - Length Overall inch	7.75 in
Dimension - N inch	0.62 in

Dimension - Pad Width inch	3.50 in
Dimension - Width inch	5.00 in
Dimension - Width mm	127 mm

Conductor Related

Conductor - AL Tube Std Size	2 1/2 IPS
Conductor - AL Tube Std Size Range	2 1/2 IPS
Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	2 1/2 IPS IPS
Conductor - Copper Tube Std Size Range	2 1/2 IPS IPS
Conductor Type	<ul style="list-style-type: none"> • AL Tube Std-Size • CU Tube Std-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50004937](#)
[Specifications - NA19A4NCG4](#)