

Substation - Aluminum Bolted Terminal

By Burndy
Catalog # [NA22A44N](#)



Substation Connectors.

Application

Substation

General

Clamping Element Design	Body and Cap
Connector Type	Terminal
Installation Torque Recommended in-lb	480 LBS/in
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	4 x 4.25 - 4 holes
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
UPC	781810119310
UPC 12 Digit	7818101193100

Dimensions

Dimension - B Length inch	6.00 in
Dimension - D inch	4.25 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	6.22 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	273 mm
Dimension - Length Overall inch	10.75 in
Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in
Dimension - Width inch	6.63 in
Dimension - Width mm	168 mm

Conductor Related

Conductor - AL Tube Std Size	4 IPS
Conductor - AL Tube Std Size Range	4 IPS
Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	4 IPS IPS
Conductor - Copper Tube Std Size Range	4 IPS IPS
Conductor Type	<ul style="list-style-type: none"> • AL Tube Std-Size • CU Tube Std-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - NA22A44N_MODEL-STEP](#)
[3D Models - NA22A44N_MODEL-IGES](#)
[3D Models - NA22A44N_MODEL-PDF](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SA038849-01](#)

