

NA20A2N, Substation - Aluminum Bolted Terminal

By Burndy
Catalog # [NA20A2N](#)

Substation Connectors.



Application

Substation

General

Catalog Number	NA20A2N
Clamping Element Design	Body and Cap
Connector Type	Terminal
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	4.38 x 3 - 2 holes
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
UPC	781810119365
UPC 12 Digit	7818101193655

Dimensions

Dimension - B Length inch	5.00 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - G inch	2.43 in
Dimension - Height inch	5.47 in
Dimension - Height mm	138.9 mm
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	211 mm
Dimension - Length Overall inch	8.31 in
Dimension - N inch	0.62 in

Dimension - Pad Width inch	4.38 in
Dimension - Width inch	5.62 in
Dimension - Width mm	143 mm

Conductor Related

Conductor - AL Tube Std Size	3 IPS
Conductor - AL Tube Std Size Range	3 IPS
Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	3 IPS IPS
Conductor - Copper Tube Std Size Range	3 IPS IPS
Conductor Type	<ul style="list-style-type: none"> • AL Tube Std-Size • CU Tube Std-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - NA20A2N_MODEL-PDF](#)
- [3D Models - NA20A2N_MODEL-IGES](#)
- [3D Models - NA20A2N_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SA038849-01](#)
- [Specifications - NA20A2N](#)