

Substation - Aluminum Bolted Terminal

By Burndy
Catalog # [NA22A4NU](#)



Substation Connectors.

Application

Substation

General

| | |
|--|--------------------|
| Clamping Element Design | Body and Cap |
| Connector Type | Terminal |
| Installation Torque Recommended in-lb | 480 LBS/in |
| Material | Aluminum Alloy |
| Material - Hardware | Aluminum |
| One Wrench Installation | Y |
| Physical Attribute - Pad Alignment | Offset |
| Physical Attribute - Pad Configuration | 5.26 x 3 - 0 holes |
| Physical Attribute - Pad Orientation | Straight |
| Plated | N |
| Plating Type | Unplated |
| UPC | 781810119396 |
| UPC 12 Digit | 7818101193966 |

Dimensions

| | |
|---|---------|
| Dimension - B Length inch | 6.00 in |
| Dimension - D inch | 3.00 in |
| Dimension - F Width Center to Center inch | 1.75 in |
| Dimension - G inch | 2.94 in |
| Dimension - Height inch | 6.22 in |
| Dimension - L Length Overall mm | 236 mm |
| Dimension - Length Overall inch | 9.31 in |
| Dimension - N inch | 0.62 in |
| Dimension - Pad Width inch | 5.25 in |
| Dimension - Width inch | 6.62 in |
| Dimension - Width mm | 168 mm |

Conductor Related

| | |
|--|--|
| Conductor - AL Tube Std Size | 4 IPS |
| Conductor - AL Tube Std Size Range | 4 IPS |
| Conductor - Connection Combination | Tube to Flat |
| Conductor - Copper Tube Std Size | 4 IPS IPS |
| Conductor - Copper Tube Std Size Range | 4 IPS IPS |
| Conductor Type | <ul style="list-style-type: none"> • AL Tube Std-Size • CU Tube Std-Size |
| Number Of Conductors | 1 |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sa038849](#)

