

NA22ACG4, Substation - Aluminum Bolted Terminal

By Burndy
Catalog # NA22ACG4



Substation Connectors.

Application

Substation

General

Catalog Number	NA22ACG4
Clamping Element Design	Body and Cap
Connector Type	Terminal
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
UPC	621945238428
UPC 12 Digit	6219452384288

Dimensions

Dimension - B Length inch	6.00 in
Dimension - D inch	3.75 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	6.22 in
Dimension - Height mm	158 mm
Dimension - L Length Overall mm	256 mm
Dimension - Length Overall inch	10.06 in
Dimension - N inch	0.88 in
Dimension - Pad Width inch	3.50 in
Dimension - Width inch	6.14 in
Dimension - Width mm	156 mm

Conductor Related

Conductor - AL Tube Std Size	4 IPS
Conductor - AL Tube Std Size Range	4 IPS
Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	4 IPS IPS
Conductor - Copper Tube Std Size Range	4 IPS IPS
Conductor Type	<ul style="list-style-type: none"> • AL Tube Std-Size • CU Tube Std-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50017924](#)
- [Specifications - NA22ACG4](#)