

NA20A44NGS, Substation - Aluminum Bolted Terminal

By Burndy
Catalog # [NA20A44NGS](#)



Substation Connectors

Application

Substation

General

Catalog Number	NA20A44NGS
Clamping Element Design	Body and Cap
Connector Type	Terminal
Installation Torque	660 LBS/in
Recommended in-lb	
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	4 x 4.25 - 4 holes
Plated	N
Plating Type	Unplated
UPC	781810351901
UPC 12 Digit	7818103519011

Dimensions

Dimension - B Length inch	5.00 in
Dimension - D inch	4.25 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - G inch	2.43 in
Dimension - Height inch	5.47 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	217 mm

Dimension - Length Overall inch	8.56 in
Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in
Dimension - Width inch	5.62 in
Dimension - Width mm	143 mm

Conductor Related

Conductor - Connection Combination	Tube to Flat
Conductor Type	<ul style="list-style-type: none"> • AL Tube Std-Size • CU Tube Std-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sa038849](#)
- [Specifications - NA20A44NGS](#)