

Substation - Aluminum Bolted Terminal

By Burndy
Catalog # [NA21ACG2](#)

Cast Aluminum Alloy Terminal, 3-1/2 IN IPS Tube to 4 Hole Pad.



Application

Substation

General

Clamping Element Design	Body and Cap
Connector Type	Terminal
Installation Torque Recommended in-lb	660 LBS/in
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	4.38 x 3 - 4 holes
Physical Attribute - Pad Orientation	Straight
Plating Type	Unplated
UPC	621945084957
UPC 12 Digit	6219450849577

Dimensions

Dimension - B Length inch	5.50 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - G inch	2.68 in
Dimension - Height inch	5.62 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	226 mm
Dimension - Length Overall inch	8.88 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	4.38 in
Dimension - Width inch	6.12 in
Dimension - Width mm	155 mm

Conductor Related

Conductor - AL Tube Std Size	3 1/2 IPS
Conductor - AL Tube Std Size Range	3 1/2 IPS
Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	3 1/2 IPS IPS
Conductor - Copper Tube Std Size Range	3 1/2 IPS IPS
Conductor Type	<ul style="list-style-type: none"> • AL Tube Std-Size • CU Tube Std-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)

