



NAS292N, 2-Hole Substation Cu Cable to Pad, #6 Sol-250 kcmil

By Burndy
Catalog # [NAS292N](#)



Cast Copper alloy terminal, 6 Sol.-250 kcmil, 5.62 in Length, Cable to Pad.

Application

Substation

General

Catalog Number	NAS292N
Clamping Element Design	Body And Cap
Connector Type	Terminal
EU RoHS Indicator	Yes
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	1.50 x 3 - 2 holes
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
Sub Brand	SUBSTATION CONNECTOR
Type	NAS
UPC	781810002360
UPC 12 Digit	7818100023600

Dimensions

Dimension - B Length fraction	2-19/50 in
Dimension - B Length inch	2.38 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	1-4/5 in
Dimension - Height inch	1.80 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	143 mm
Dimension - Length Overall inch	5.62 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.50 in
Dimension - Width inch	2.00 in
Dimension - Width mm	51 mm

Conductor Related

Conductor - Connection Combination	Cable to Flat
Conductor - Copper Solid Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	6 AWG-4/0 AWG
Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	6 AWG-250 kcmil
Conductor - Large Groove Max	250 kcmil
Conductor - Large Groove Min	2/0 str
Conductor - Small Groove Max	1/0 str
Conductor - Small Groove Min	6 sol
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size
Number of Conductors	1

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - NAS292N_MODEL-PDF](#)

[3D Models - NAS292N_MODEL-STEP](#)

[3D Models - NAS292N_MODEL-IGES](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section L - Bolted](#)

[Substation](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_NAS292N_LineArt](#)

[Sales Drawings - SE079584-01](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-NAS292N-SPEC-EN | REV 8/2024