

Substation - Aluminum Bolted T Connector

By Burndy
Catalog # [NNT17A15A](#)



Substation Connectors.

Application

Substation

General

Catalog Number	NNT17A15A
Connector Type	T-Connector
Installation Torque	300 LBS/in
Recommended in-lb	
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Orientation	90 Degree
Plated	N
Plating Type	Unplated
Type	Bolted Tees
UPC	781810119464
UPC 12 Digit	7818101194644

Dimensions

Dimension - B Length inch	4.00 in
Dimension - Height inch	3.88 in
Dimension - L Length Overall mm	187 mm
Dimension - Length BB inch	3.50 in
Dimension - Length Overall inch	7.38 in
Dimension - Width inch	3.06 in

Dimension - Width mm 78 mm

Conductor Related

Conductor - AL Tube Std Run	1 1/2 IPS
Conductor - AL Tube Std Run Range	1 1/2 IPS
Conductor - AL Tube Std Tap	1 IPS
Conductor - AL Tube Std Tap Range	1 IPS
Conductor - Connection Combination	Tube to Tube
Conductor Type	<ul style="list-style-type: none"> • AL Tube Std-Run • AL Tube Std-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Minimum Pack Quantity 2

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sc064838](#)
- [Specifications - NNT17A15A](#)