

Substation - Aluminum Bolted T Connector

By Burndy
Catalog # [NNT21A20A](#)



Cast Al Alloy T Connector, 11.06 IN L, 5.63 IN W, Tube to Tube, 3-1/2 IN Al IPS (Run) , 3 IN Al IPS (Tap), 5/8 IN-11 Bolt Size.

Application

Substation

General

Catalog Number	NNT21A20A
Connector Type	T-Connector
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Plated	N
Plating Type	Unplated
Type	Bolted Tees
UPC	781810004050
UPC 12 Digit	7818100040500

Dimensions

Dimension - B Length fraction	5-1/2 in
Dimension - B Length inch	5.50 in
Dimension - Height fraction	5-5/8
Dimension - Height inch	5.56 in
Dimension - L Length Overall mm	281 mm
Dimension - Length BB inch	5.00 in
Dimension - Length Overall inch	11.06 in
Dimension - Width inch	5.63 in
Dimension - Width mm	143 mm

Conductor Related

Conductor - AL Tube Std Run	3 1/2 IPS
Conductor - AL Tube Std Run Range	3 1/2 IPS
Conductor - AL Tube Std Tap	3 IPS
Conductor - AL Tube Std Tap Range	3 IPS
Conductor - Connection Combination	Tube to Tube
Conductor Type	<ul style="list-style-type: none"> • AL Tube Std-Run • AL Tube Std-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_FNNT_LineArt](#)
- [Sales Drawings - sc064838](#)
- [Specifications - NNT21A20A](#)