

# Substation - Aluminum Bolted T Connector

By Burndy  
Catalog # [NNT15A14A](#)



Substation Connectors.

## Application

Substation

## General

Catalog Number	NNT15A14A
Connector Type	T-Connector
Installation Torque	300 LBS/in
Recommended in-lb	
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Orientation	90 Degree
Plated	N
Plating Type	Unplated
Type	Bolted Tees
UPC	781810328095
UPC 12 Digit	7818103280955

## Dimensions

Dimension - B Length inch	3.50 in
Dimension - Height inch	3.38 in
Dimension - Height mm	85.9 mm
Dimension - L Length Overall mm	167 mm
Dimension - Length BB inch	3.25 in
Dimension - Length Overall inch	6.56 in
Dimension - Width inch	2.81 in

Dimension - Width mm 71 mm

## Conductor Related

Conductor - AL Tube Std Run	1 IPS
Conductor - AL Tube Std Run Range	1 IPS
Conductor - AL Tube Std Tap	3/4 IPS
Conductor - AL Tube Std Tap Range	3/4 IPS
Conductor - Connection Combination	Tube to Tube
Conductor Type	<ul style="list-style-type: none"> <li>• AL Tube Std-Run</li> <li>• AL Tube Std-Tap</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

## Logistics

Minimum Pack Quantity 1

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sc064838](#)
- [Specifications - NNT15A14A](#)