

Substation - Copper Coupler - Straight

By Burndy
Catalog # NS1414HC

Cast Cu Alloy Bolted Coupler, Cu Tube to Tube, 3/4" IPS, Silicon Bronze H/W.



Application

Substation

General

Catalog Number	NS1414HC
Connector Type	Couplers
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material - Hardware	Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
Type	Tube to Tube Couplers
UPC	781810002766
UPC 12 Digit	7818100027666

Dimensions

Dimension - B Length inch	2.69 in
Dimension - Height inch	2.61 in
Dimension - Height mm	58.9 mm
Dimension - L Length Overall mm	137 mm
Dimension - Length BB inch	2.69 in
Dimension - Length Overall inch	5.38 in
Dimension - Width inch	2.81 in
Dimension - Width mm	71 mm

Conductor Related

Conductor - Connection Combination	Tube to Tube
Conductor - Copper Tube Std Run	3/4 IPS
Conductor - Copper Tube Std Size	3/4 IPS
Conductor - Copper Tube Std Size Range	3/4 IPS
Conductor - Copper Tube Std Tap	3/4 IPS
Conductor Type	CU Tube Std-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - NS1414HC_MODEL-IGES](#)
- [3D Models - NS1414HC_MODEL-PDF](#)
- [3D Models - NS1414HC_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30017047](#)
- [Specifications - NS1414HC](#)