



Substation - Aluminum Bolted T Connector

By Burndy
Catalog # [NNT18A18A](#)

Cast Al Alloy T Connector, 9.06 IN L, 4.50 IN W, Tube to Tube, 2 IN IPS Al (Run), 2 IN IPS Al (Tap), 5/8 IN-11 Bolt Size Dia.



Application

Substation

General

Connector Type	T-Connector
Installation Torque Recommended in-lb	480 LBS/in
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Orientation	90 Degree
Plated	N
Plating Type	Unplated
Type	Bolted Tees
UPC	781810004036
UPC 12 Digit	7818100040366

Dimensions

Dimension - B Length fraction	4-1/4 in
Dimension - B Length inch	4.25 in
Dimension - Height fraction	4-1/2 in
Dimension - Height inch	4.44 in
Dimension - L Length Overall mm	230 mm
Dimension - Length BB inch	4.25 in
Dimension - Length Overall inch	9.06 in
Dimension - Width inch	4.50 in
Dimension - Width mm	114 mm

Conductor Related

Conductor - AL Tube Std Run	2 IPS
Conductor - AL Tube Std Run Range	2 IPS
Conductor - AL Tube Std Tap	2 IPS
Conductor - AL Tube Std Tap Range	2 IPS
Conductor - Connection Combination	Tube to Tube
Conductor Type	<ul style="list-style-type: none">AL Tube Std-RunAL Tube Std-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_FNNT_LineArt](#)
[Sales Drawings - sc064838](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-NNT18A18A-SPEC-EN | REV 5/2024