

Substation - Aluminum Bolted T Connector

By Burndy
Catalog # [NNT22A17A75](#)



Substation Connectors.

Application

Substation

General

| | |
|---|----------------|
| Catalog Number | NNT22A17A75 |
| Connector Type | A-Frame |
| Installation Torque | 300 LBS/in |
| Recommended in-lb | |
| Material | Aluminum Alloy |
| Material - Hardware | Aluminum |
| One Wrench Installation | Y |
| Physical Attribute - Number of Run Conductors | 1 |
| Physical Attribute - Number of Tap Conductors | 1 |
| Physical Attribute - Pad Orientation | 75 Degree |
| Plated | N |
| Plating Type | Unplated |
| Type | Bolted Tees |
| UPC | 781810106433 |
| UPC 12 Digit | 7818101064333 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - B Length inch | 4.00 in |
| Dimension - Height inch | 5.00 in |
| Dimension - L Length Overall mm | 278 mm |
| Dimension - Length BB inch | 4.00 in |
| Dimension - Length Overall inch | 10.96 in |

| | |
|------------------------|---------|
| Dimension - Width inch | 4.00 in |
| Dimension - Width mm | 102 mm |

Conductor Related

| | |
|-----------------------------------|--|
| Conductor - AL Tube Std Run | 4 IPS |
| Conductor - AL Tube Std Run Range | 4 IPS |
| Conductor - AL Tube Std Tap | 1 1/2 IPS |
| Conductor - AL Tube Std Tap Range | 1 1/2 IPS |
| Conductor Type | <ul style="list-style-type: none"> • AL Tube Std-Run • AL Tube Std-Tap |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 208098-03](#)
- [Specifications - NNT22A17A75](#)