

Substation - Aluminum Bolted T Connector

By Burndy
Catalog # [NNT22A22A](#)



Substation Connectors.

Application

Substation

General

Catalog Number	NNT22A22A
Connector Type	T-Connector
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Orientation	90 Degree
Plated	N
Plating Type	Unplated
Type	Bolted Tees
UPC	781810054369
UPC 12 Digit	7818100543699

Dimensions

Dimension - B Length fraction	6 in
Dimension - B Length inch	6.00 in
Dimension - Height fraction	6-1/4
Dimension - Height inch	6.19 in
Dimension - Height mm	157.2 mm
Dimension - L Length Overall mm	321 mm
Dimension - Length BB inch	6.00 in
Dimension - Length Overall inch	12.63 in
Dimension - Width inch	6.63 in

Dimension - Width mm 168 mm

Conductor Related

Conductor - AL Tube Std Run	4 IPS
Conductor - AL Tube Std Run Range	4 IPS
Conductor - AL Tube Std Tap	4 IPS
Conductor - AL Tube Std Tap Range	4 IPS
Conductor - Connection Combination	Tube to Tube
Conductor Type	<ul style="list-style-type: none"> • AL Tube Std-Run • AL Tube Std-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity 1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sc064838](#)
- [Specifications - NNT22A22A](#)