

# Substation - Copper T Connector - 90 Degrees

By Burndy  
Catalog # NSNT1329

Substation Connectors.



## Application

Substation

## General

Catalog Number	NSNT1329
Connector Type	T-Connector
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Plated	N
Plating Type	Unplated
Type	Tube to Cable Couplers
UPC	781810077498
UPC 12 Digit	7818100774988

## Dimensions

Dimension - B Length inch	2.00 in
Dimension - Height inch	2.00 in
Dimension - Height mm	50.8 mm
Dimension - L Length Overall mm	129 mm
Dimension - Length BB inch	2.38 in
Dimension - Length Overall inch	5.08 in
Dimension - Width fraction	1-24/25 in
Dimension - Width inch	1.96 in
Dimension - Width mm	50 mm

## Conductor Related

Conductor - Connection Combination	Tube to Cable
Conductor - Copper Solid Tap	5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0

Conductor - Copper Solid Tap Range	AWG;4/0 AWG 5 AWG-4/0 AWG
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Tap Range	6 AWG-250 kcmil
Conductor - Copper Tube Std Run	1/2 IPS
Conductor - Copper Tube Std Run Range	1/2 IPS
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Run</li> <li>• CU C Solid-Run</li> <li>• CU C Str-Tap</li> <li>• CU C Solid-Tap</li> <li>• CU Tube Std-Run</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	15
-----------------------	----

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - NSNT1329](#)