

Substation - Copper Coupler - Straight

By Burndy
Catalog # NS1919



Cast Cu Alloy Bolted Coupler, Cu Tube to Tube, 2-1/2" IPS, Silicon Bronze H/W.

Application

Substation

General

Catalog Number	NS1919
Connector Type	Couplers
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material - Hardware	Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
Type	Tube to Tube Couplers
UPC	781810002568
UPC 12 Digit	7818100025688

Dimensions

Dimension - B Length inch	2.88 in
Dimension - Height inch	3.88 in
Dimension - Height mm	98.6 mm
Dimension - L Length Overall mm	146 mm
Dimension - Length BB inch	2.88 in
Dimension - Length Overall inch	5.75 in
Dimension - Width inch	5.25 in
Dimension - Width mm	133 mm

Conductor Related

Conductor - Connection Combination	Tube to Tube
Conductor - Copper Tube Std Run	2 1/2 IPS
Conductor - Copper Tube Std Size	2 1/2 IPS
Conductor - Copper Tube Std Size Range	2 1/2 IPS
Conductor - Copper Tube Std Tap	2 1/2 IPS
Conductor Type	CU Tube Std-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

- [3D Models - NS1919_MODEL-PDF](#)
- [3D Models - NS1919_MODEL-STEP](#)
- [3D Models - NS1919_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_NS_LineArt](#)
- [Sales Drawings - sa011052-01](#)
- [Specifications - NS1919](#)