

Substation - Copper T Connector - 90 Degrees

By Burndy
Catalog # NSNT1429

Cast Cu Alloy T Connector, Cu Tube to Cable, 3/4 IN IPS (Run), 6 AWG Sol. to 250 kcmil (Tap).



Application

Substation

General

Catalog Number	NSNT1429
Connector Type	T-Connector
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material - Hardware	Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Plated	N
Plating Type	Unplated
Type	Tube to Cable Couplers
UPC	781810003022
UPC 12 Digit	7818100030222

Dimensions

Dimension - B Length inch	2.00 in
Dimension - Height inch	2.00 in
Dimension - L Length Overall mm	129 mm
Dimension - Length BB inch	2.38 in
Dimension - Length Overall inch	5.08 in
Dimension - Width fraction	1-24/25 in
Dimension - Width inch	1.96 in
Dimension - Width mm	50 mm

Conductor Related

Conductor - Connection Combination	Tube to Cable
------------------------------------	---------------

Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Solid Tap Range	6 AWG-1 AWG
Conductor - Copper Str Tap	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Tap Range	1/0 AWG-250 kcmil
Conductor - Copper Tube Std Run	3/4 IPS
Conductor - Copper Tube Std Run Range	3/4 IPS
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU C Solid-Run • CU C Str-Tap • CU C Solid-Tap • CU Tube Std-Run

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - se..087856-01](#)
- [Specifications - NSNT1429](#)