



4.5-Ton OEM Pneumatic Bench Press, #8 AWG - 4/0 AWG

By Burndy
Catalog # [OEM840NCP](#)

4.5T OEM Pneumatic Bench Press.

Features

- Customizable clear safety guard for left, right, or front feed cable entry
- Guarded foot switch
- Adjustable connector locator
- Cycle counter
- Accommodates UM, U and W dies

Application

Crimping

General

Application - For Use On	Use with UM, U and W Dies
Catalog Number	OEM840NCP
Die Type	UM Die
Tool Type	Pneumatic Press
Type	Crimper
UPC	781810660379

Dimensions

Dimensions	18.56 in x 10.26 in x 22.01 in
Height	22.01 in
Length	18.56 in



Weight	61 lb
Width	10.26 in

Conductor Related

Crimping Ranges	Installs #8 - 4/0 AWG
-----------------	-----------------------

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Bench Press, foot switch (accessories sold separately)

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - Cutters](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50024706](#)
- [SDS - Non-Detergent Motor Oil SDS \(2013-06\)](#)
- [Specifications - OEM840NCP](#)
- [Video - BURNDY OEM840NCP OEM Tool](#)