



PENHT5GAL, Oxide Inhibitor, 5 Gallon Container

By Burndy
Catalog # [PENHT5GAL](#)



Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

General

| | |
|----------------|-----------|
| Catalog Number | PENHT5GAL |
| Container Type | Pail |
| Pour Point | -58 °F |
| Trade Name | PENETROX™ |

UPC 781810476581
UPC 12 Digit 7818104765811

Certifications And Compliance

| | |
|-------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance | UI |
| Status | |
| UL Listed | No |

Logistics

| | |
|-----------------------|----------|
| Container Size | 5 Gallon |
| Minimum Pack Quantity | 1 |

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - PENHT5GAL](#)