



Full Cycle Hand Operated Ratchet Crimper, 8000 lbs Crimp Force, #8 AWG - 250 kcmil Copper, #8 AWG - #4/0 AWG Aluminum

By Burndy
Catalog # [OUR840](#)



Full Cycle Ratchet Crimper, #8-250 kcmil CU, #8-4/0 AWG AL.

Features

- Spring loaded positive lock die retainer buttons
- 1/4 hole for snap fastener
- Butting surfaces provide visual check for tool adjustments
- Spring loaded handle
- High strength steel
- Rugged and protected ratchet mechanism
- Heat treated steel construction
- Comfort grip handles

Application

Crimping

General

Application - For Use On	Use with X Dies
Die Type	W Die and X Die
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Trade Name	POPPER™ HYTOOL™
UPC	781810408537
UPC 12 Digit	7818104085377

Dimensions

Dimensions	13.00 in x 3.75 in x 1.30 in
Height	1.30 in
Length	13.00 in
Weight	2.875 lb
Width	3.75 in

Conductor Related

Crimping Ranges	Copper: #8 AWG - 250 kcmil; Aluminum: #8 AWG to 4/0 AWG
-----------------	--

Certifications and Compliance

Standards - RoHS Compliance	EX
Status	

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sc210647-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-OUR840-SPEC-EN | REV 1/2024