

## Cutting Die for use in 15-Ton, 1.2" max diameter

By Burndy  
Catalog # P15K



15T Cutting Die, 1.2" max diameter.

### Application

Cutting

### General

Application - For Use On	Maximum Cutting Diameter: 795 kcmil ACSR; 750 kcmil Copper/Aluminum with 1.20" dia over Insulation; 1.20" dia Bare Copper/Aluminum
Catalog Number	P15K
Crimp Force Capacity	15 ton
Die Type	P Die
EU RoHS Indicator	Yes
Sub Brand	Tool
Type	Die
UPC	781810008720
UPC 12 Digit	7818100087200

### Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance Status	EX

### Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	891

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_P15K\\_LineArt](#)  
[Sales Drawings - SD73451](#)  
[Specifications - P15K](#)