



## Q2A262N, Two Conductor Two Hole Mounting Heavy Duty Copper Lug Connector, 1/0-2/0 AWG Str, 1/2" Stud, 3/4" Spacing, 2 Screws

By Burndy  
Catalog # [Q2A262N](#)



Copper Terminal, 2 Hole, 1/0-2/0 AWG (Str), 1/2" Stud, 3/4" Stud Hole Spacing, 2 Screws.

### Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

### Application

For Copper Cable

### General

Catalog Number	Q2A262N
Connector Type	Duel Clamp
EU RoHS Indicator	Yes
Installation Torque	180 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810321249
UPC 12 Digit	7818103212499

### Dimensions

Dimension - B Length inch	4.19 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.12 in
Dimension - F Width Center to Center inch	0.69 in
Dimension - Height fraction	1-3/16 in
Dimension - Height inch	1.19 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	106 mm
Dimension - Length Overall inch	4.19 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.62 in
Dimension - Stud Size inch	1/2
Dimension - Width fraction	1-15/16 in
Dimension - Width inch	1.94 in

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - Copper Str Size	1/0 ;2/0 AWG
Conductor - Copper Str Size Range	1/0 -2/0 AWG
Conductor Size	1/0-2/0 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity 1

## Product Assets

[3D Models - Q2A262N\\_MODEL-IGES](#)

[3D Models - Q2A262N\\_MODEL-PDF](#)

[3D Models - Q2A262N\\_MODEL-STEP](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR\\_Q2A284N\\_LineArt](#)

[Sales Drawings - sd023314-01](#)

[Specifications - Q2A262N](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-Q2A262N-SPEC-EN | REV 8/2024