



Q2B314N, Two Conductor Four Hole Mounting Heavy Duty Copper Lug Connector, 250-350 kcmil, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [Q2B314N](#)



Cast Cu Alloy QIKLUG Terminals, 4-Nema Holes, 250 - 350 kcmil Cu.

Features

- QIKLUG™ terminals for copper cable
- High copper alloy
- Q2B style lugs join two cables at right angles to a single terminal block
- Each element accommodates a range of cable
- One-wrench installation

General

Connector Type	Right Angle
Material	Copper
Physical Attribute - Number of Holes	4
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810338650
UPC 12 Digit	7818103386500

Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.19 in
Dimension - D inch	3.56 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	1-17/25 in
Dimension - Height inch	1.69 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - Length Overall inch	5.88 in
Dimension - Pad Width inch	3.00 in

Electrical Ratings

Rating - Minimum Voltage 600

Conductor Related

Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil
Conductor - Copper Str Size Range	250 kcmil-350 kcmil
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - sc023381-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-Q2B314N-SPEC-EN | REV 6/2024

