

# QA262N, Heavy Duty Two Hole Mounting Copper Lug Connector, 2/0-1/0 Str, 1/2" Stud, 1-3/4" Spacing



By Burndy  
Catalog # [QA262N](#)

Cast Copper Alloy Qiklug, 2/0 Str.-1/0 Str.

## Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

## General

Catalog Number	QA262N
Connector Type	Single Clamp
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type Plated	Hexagonal Bolt N
Plating Type	Unplated
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810314524
UPC 12 Digit	7818103145244

## Dimensions

Dimension - B Length fraction	47/50 in
Dimension - B Length inch	0.94 in
Dimension - Bolt Size fraction	1/2
Dimension - Cross Flats inch	0.69 in
Dimension - D inch	3.12 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	1-4/25 in
Dimension - Height inch	1.16 in
Dimension - Height mm	29.5 mm
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	106 mm
Dimension - Length Overall inch	4.19 in

Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.00 in
Dimension - Width inch	0.81 in

## Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

## Conductor Related

Conductor - Copper Str Size	1/0 ;2/0 AWG
Conductor - Copper Str Size Range	1/0 -2/0 AWG
Conductor Size	2/0-1/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Str Navy-Size</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	7
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_QA\\_LineArt](#)
- [Sales Drawings - SC23464-01\\_B](#)
- [Specifications - QA262N](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-QA262N-SPEC-EN | REV 10/2024