



QB26, Right Angled Heavy Duty Copper Lug Connector, 1/0-2/0 AWG Str, 3/8" Stud, 1 Screw

By Burndy
Catalog # [QB26](#)



Copper Terminal, Side Entrance, 1 Hole, 1/0-2/0 AWG (Str), 3/8" Stud, 1 Screw.

Features

- Side Entry terminal
- Joins a range of cable at right angles to terminal blocks
- One-wrench installation

Application

For Joining A Range Of Copper Cable At Right Angles To Terminal Blocks

General

Catalog Number	QB26
Connector Type	Right Angle
EU RoHS Indicator	Yes
Installation Torque	180 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Clamping Elements	1
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810324288

Dimensions

Dimension - B Length fraction	47/50 in
Dimension - B Length inch	0.94 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.00 in
Dimension - Height fraction	1-1/8
Dimension - Height inch	1.13 in
Dimension - Hole Size fraction	13/32
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in
Dimension - N inch	0.44 in
Dimension - Pad Width fraction	13/16 in
Dimension - Pad Width inch	0.81 in
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Dimension - Width inch	0.81 in
Dimension - Width mm	21 mm
Weight	0.23 lb

Conductor Related

Conductor - Copper Str Size	1/0 ;2/0 AWG
Conductor - Copper Str Size Range	1/0 -2/0 AWG
Conductor Size	1/0-20 AWG
Conductor Type	CU C Str-Size
Number of Conductors	1

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[3D Models - QB26_MODEL-PDF](#)

[3D Models - QB26_MODEL-IGES](#)

[3D Models - QB26_MODEL-STEP](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_QB_LineArt](#)

[Sales Drawings - sa06068-01](#)

[Specifications - QB26](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-QB26-SPEC-EN | REV 8/2024