



# PATRIOT® T3 Technology 12-Ton Battery Crimper, C-Head, Uncovered, (2) 3.0Ah 18V Li-Ion Batteries, 120V-AC Charger, Nylon Pro Bag



By Burndy  
Catalog # [PAT750T3U03A3](#)

PA750T3 Tech 12T Battery Crimper, C-Head, Uncovered, 3Ah Li-ion, AC, Nylon Pro Bag.

## Features

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- C-head with 1.65" jaw opening with 355° head rotation
- Used with U dies
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

## Application

Crimping

## General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT750T3U03A3
Container Type	Nylon Pro Bag
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Contact Manufacturer
Power Source	120V-AC Charger
Recharge Time	0.5 h
Tool Type	Battery Actuated Crimper, T3 Technology
Trade Name	PATRIOT®
Type	Crimper

UPC	621945561007
UPC 12 Digit	621945561007

## Dimensions

Dimensions	15.75 in x 3.25 in x 14.75 in
Height	14.75 in
Jaw Width	1.65 in
Length	15.75 in
Weight	14.85 lb
Width	3.25 in

## Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

## Conductor Related

Crimping Ranges	Copper: #14 sol. - 750 kcmil; Aluminum: #8 sol. - 750 kcmil; ACSR: #4 AWG - 556.5 kcmil; Ground Rod: 1/2" - 1" diameter
-----------------	--

## Certifications And Compliance

Buy American Compliant	Contact Manufacturer
------------------------	----------------------

## Logistics

Carton Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50106314](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Specifications - PAT750T3U03A3](#)

[Video - BURNDY T3 APP Features and Benefits](#)  
[Video - BURNDY T3 Is Here - PAT750T3](#)

[Video - BURNDY T3 APP Install & Register](#)



©2024 Hubbell Incorporated. All rights reserved  
BRDY-PAT750T3U03A3-SPEC-EN | REV 10/2024