



# PATRIOT® 1500 Series Battery Cutter for Copper and Aluminum, (1) 3.0Ah 18V Li-ion Battery, 120V-AC Charger, Nylon Pro Bag

By Burndy  
Catalog # PATCUT1500LIPB



PATCUT1500 Battery Cutter for CU/AL, 3Ah Li-ion, AC, Nylon Pro Bag.

## Features

- Variable speed trigger
- Forward/Reverse switch features a locking position
- Large, strategically placed, non-skid bumper
- LED Worklight
- Accepts 2.0Ah-6.0Ah Makita batteries

## Application

Cutting

## General

Application - For Use On	Aluminum, Copper Cable
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Nylon Pro Bag
EU RoHS Indicator	No
Power Source	120V-AC Charger
Recharge Time	0.5 h
Sub Brand	PATRIOT® Cutter
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutter
UPC	621945562394
UPC 12 Digit	621945562394

## Dimensions

Dimensions	6.00 in x 4.38 in x 15.50 in
Height	15.50 in
Length	6.00 in
Weight	6.90 lb
Width	4.38 in

## Electrical Ratings

Operating Voltage 18 VDC

## Conductor Related

Crimping Ranges Cutting Capacity: Aluminum up to 1500 kcmil, Copper (Soft Drawn) up to 1000 kcmil (Do Not Cut Steel or ACSR)

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Cutter, (1) Battery, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12

## Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50106125](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Video - PATCUT1500 Series Cutter](#)
- [Video - BURNDY Pro Bag, BURNDY Minute](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-PATCUT1500LIPB-SPEC-EN | REV 1/2024