

## QB8C, Right Angled Heavy Duty Copper Lug Connector, #14 AWG Sol-8 AWG Str, #10 Stud, 1 Screw

By Burndy  
Catalog # [QB8C](#)



Copper Terminal, Side Entrance, 1 Hole, 14 AWG (Sol)-8 AWG (Str), #10 Stud, 1 Screw.

### Features

- Side Entry terminal
- Joins a range of cable at right angles to terminal blocks
- One-wrench installation

### General

Catalog Number	QB8C
Connector Type	Right Angle
Installation Torque	75 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Clamping Elements	1
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810324257

### Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Bolt Size fraction	#10
Dimension - D inch	0.56 in
Dimension - Height fraction	7/8 in
Dimension - Height inch	0.88 in
Dimension - Hole Size fraction	7/32
Dimension - Hole Size inch	0.22 in
Dimension - Hole Size mm	6 mm
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.13 in
Dimension - N inch	0.28 in
Dimension - Pad Width fraction	9/16 in
Dimension - Pad Width inch	0.56 in
Dimension - Stud Size fraction	#10
Dimension - Stud Size inch	#10
Dimension - Width inch	0.56 in
Dimension - Width mm	14 mm

### Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Solid Size Range	14 AWG-8 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Size Range	14 AWG-8 AWG
Conductor Size	14-8 AWG
Conductor Type	CU C Str-Size
Number of Conductors	1

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity 33

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_QB\\_LineArt](#)  
[Sales Drawings - sa06068-01](#)  
[Specifications - QB8C](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-QB8C-SPEC-EN | REV 8/2024