

QPX28R28R, Heavy Duty Copper Tapping Connector

By Burndy
Catalog # QPX28R28R



VERSITAP™ Mechanical Parallel Clamp.

Features

- VERSITAP™ Type QPX-Y Parallel Clamps for copper or aluminum are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

General

Catalog Number	QPX28R28R
Connector Type	Universal Clamp
Material	Aluminum
Material - Hardware	DURIUM™ Silicon Bronze
Number Of Ports	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	VERSITAP™
UPC	781810097137
UPC 12 Digit	7818100971377

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2.06 in
Dimension - Height fraction	2-1/2 in
Dimension - Height inch	2.56 in
Dimension - Width inch	2.06 in
Dimension - Width mm	52 mm

Electrical Ratings

Rating - Minimum Voltage 600

Conductor Related

Conductor - AL Str Run	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	1/0 AWG-4/0 AWG
Conductor - AL Str Tap	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Tap Range	1/0 AWG-4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_QPX_PARA_CLAMP_LineArt Specifications - QPX28R28R](#)