

QPX2C2C, Heavy Duty Copper Tapping Connector, Run #6-#2 AWG; Tap #6-#2 AWG

By Burndy
Catalog # QPX2C2C



VERSITAP™ Mechanical Parallel Clamp for Copper;
Accommodates: Run: #6 - #2 AWG; Tap: #6 - #2 AWG.

Features

- VERSITAP™ Type QPX Parallel Clamps for copper are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Application

For Tee, Cross, Parallel, Butt And Tap Connections, Copper

General

Catalog Number	QPX2C2C
Connector Type	Universal Clamp
EU RoHS Indicator	Yes
Installation Torque	180 LBS/in
Recommended in-lb	
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	VERSITAP
Temperature Rating	194
Trade Name	VERSITAP™
Type	QPX
UPC	781810341506
UPC 12 Digit	7818103415066

Dimensions

Dimension - B Length fraction	1/3 in
Dimension - B Length inch	0.31 in
Dimension - Height fraction	1-1/2
Dimension - Height inch	1.5
Dimension - Height mm	38.1 mm
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.31 in

Dimension - Width fraction	1-3/8 in
Dimension - Width inch	1.38
Dimension - Width mm	35 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Run Range	6 AWG-2 AWG
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor - Nominal Diameter	0.179, 0.182, 0.184, 0.199, 0.206, 0.219, 0.223, 0.225, 0.230, 0.232, 0.246, 0.258, 0.260, 0.276, 0.290, 0.310, 0.320, 0.326
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU C Str-Tap

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - QPX2C2C_MODEL-PDF](#)

[3D Models - QPX2C2C_MODEL-STEP](#)

[3D Models - QPX2C2C_MODEL-IGES](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) -](#)

[BUR_QPX_PARA_CLAMP_LineArt](#)

[Sales Drawings - sa007887-01](#)

[Specifications - QPX2C2C](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-QPX2C2C-SPEC-EN | REV 10/2024