



QPX3428, Heavy Duty Copper Tapping Connector, 250-500 kcmil (Run), 1-4/0 AWG (Tap)

By Burndy
Catalog # QPX3428



VERSITAP™ Mechanical Parallel Clamp for Copper;
Accommodates: Run: 250 - 500 kcmil; Tap: #1 - 4/0 AWG.

Features

- VERSITAP™ Type QPX Parallel Clamps for copper are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Application

For Tee, Cross, Parallel, Butt And Tap Connections, Copper

General

Catalog Number	QPX3428
Connector Type	Universal Clamp
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	VERSITAP
Temperature Rating	194
Trade Name	VERSITAP™
Type	QPX
UPC	781810343258
UPC 12 Digit	7818103432588

Dimensions

Dimension - Height fraction	2-3/4
Dimension - Height inch	2.75
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - Width fraction	2-1/16 in
Dimension - Width inch	2.06
Dimension - Width mm	52 mm

Electrical Ratings

Rating - Minimum Voltage 600

Conductor Related

Conductor - Copper Str Run	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	250 kcmil-500 kcmil
Conductor - Copper Str Tap	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Tap Range	1 AWG-4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU C Str-Tap

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[3D Models - QPX3428_MODEL-STEP](#)

[3D Models - QPX3428_MODEL-PDF](#)

[3D Models - QPX3428_MODEL-IGES](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) -](#)

[BUR_QPX_PARA_CLAMP_LineArt](#)

[Sales Drawings - sa007887-01](#)

[Specifications - QPX3428](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-QPX3428-SPEC-EN | REV 8/2024