

QPX4444, Heavy Duty Copper Tapping Connector, Run & Tap: 500-1000 kcmil

By Burndy
Catalog # [QPX4444](#)



VERSITAP™ Mechanical Parallel Clamp for Copper;
Accommodates: Run: 500 - 1000 kcmil; Tap: 500 - 1000 kcmil.

Features

- VERSITAP™ Type QPX Parallel Clamps for copper are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Application

For Tee, Cross, Parallel, Butt And Tap Connections

General

Catalog Number	QPX4444
Connector Type	Universal Clamp
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	VERSITAP
Temperature Rating	194
Trade Name	VERSITAP™
Type	QPX
UPC	781810345757
UPC 12 Digit	7818103457577

Dimensions

Dimension - Height fraction	3-7/16
Dimension - Height inch	3.44
Dimension - Height mm	87.4 mm
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.62 in
Dimension - Width fraction	2-9/16 in
Dimension - Width inch	2.56
Dimension - Width mm	65 mm

Electrical Ratings

Rating - Minimum Voltage 600

Conductor Related

Conductor - Copper Str Run	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Run Range	500 kcmil-1000 kcmil
Conductor - Copper Str Tap	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Tap Range	500 kcmil-1000 kcmil
Conductor - Nominal Diameter	0.162, 0.813, 0.893, 0.893, 0.964, 0.998, 1.031, 1.031, 1.094, 1.151
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU C Str-Tap

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[3D Models - QPX4444_MODEL-PDF](#)

3D Models - QPX4444_MODEL-IGES
3D Models - QPX4444_MODEL-STEP
Catalogs - BURNDY Master Catalog - Section A - Mechanical
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice

Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) -
BUR_QPX_PARA_CLAMP_LineArt
Sales Drawings - sa007887-01
Specifications - QPX4444



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-QPX4444-SPEC-EN | REV 10/2024