



## PENA1/2, Oxide Inhibitor, .5 ounce

By Burndy  
Catalog # [PENA1/2](#)

Oxide Inhibiting Electrical Joint Compound, 1/2 OZ, For Al-Al, Al-Cu & Al Conduit Threads.



### Application

For Aluminum To Copper, Aluminum To Aluminum, Aluminum To Conduit

### General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Catalog Number	PENA1/2
Container Type	Tube
EU RoHS Indicator	Yes
Pour Point	-15 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
Type	A
UPC	781810592601
UPC 12 Digit	7818105926011
Viscosity at 100 Fahrenheit	305 °F

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	50
Container Size	1/2 oz
Minimum Pack Quantity	50

### Product Assets

- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_PENA\\_LineArt](#)
- [Sales Drawings - sc211487-01](#)
- [SDS - PENETROX A ESPANOL SDS](#)
- [SDS - PENETROX A FRENCH SDS](#)
- [SDS - PENETROX A PORTUGUESE SDS](#)
- [SDS - PENETROX A SDS](#)
- [SDS - PENETROX A ESTONIAN SDS](#)
- [SDS - PENETROX A GERMAN SDS \(GHS\) \(2019-07\)](#)
- [Specifications - PENA1/2 Specification Sheet](#)
- [Specifications - PENA1/2](#)
- [Specifications - Burndy\\_PENA12\\_Specsheet](#)