



QQA312N, Twin Clamping Two Hole Mounting Heavy Duty Copper Lug Connector

By Burndy
Catalog # [QQA312N](#)

Copper Terminal, Heavy Duty, 2 Hole, 250-350 kcmil, 1/2" Stud,
1-3/4" Stud Hole Spacing, 2 Screws.



Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Application

For Copper Cable

General

Catalog Number	QQA312N
Connector Type	Duel Clamp
EU RoHS Indicator	Yes
Installation Torque	325 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type Plated	Hexagonal Bolt N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810326008

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.13 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	1.6896551724137931 in
Dimension - Height inch	1.69 in
Dimension - Height mm	42.9 mm
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	149 mm

Dimension - Length Overall inch	5.88 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.19 in

Conductor Related

Conductor - Copper Str Navy Size	250 (61) Navy;300 (91) Navy;350 (91) Navy
Conductor - Copper Str Navy Size Range	250 (61) Navy-350 (91) Navy
Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil
Conductor - Copper Str Size Range	250 kcmil-350 kcmil
Conductor Size	250-350 kcmil
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Str Navy-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_QQA_LineArt](#)
[Sales Drawings - SA..005911-01](#)
[Specifications - QQA312N](#)

