



PENA1255GAL, Oxide Inhibitor, 55 Gallon

By Burndy
Catalog # [PENA1255GAL](#)



Penetrox Oxide Inhibitor Reformulations.

Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

General

Catalog Number	PENA1255GAL
Container Type	Drum
Pour Point	-15 °F
Trade Name	PENETROX™
UPC	781810105870
UPC 12 Digit	7818101058700

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Container Size	55 Gallon
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[SDS - PENETROX A-12 SDS](#)
[SDS - PENETROX A-12 ESPANOL SDS](#)
[SDS - PENETROX A SDS](#)
[SDS - PENETROX A FRENCH SDS](#)
[Specifications - PENA1255GAL](#)