



PENA1/2, Oxide Inhibitor, .5 ounce

By Burndy
Catalog # [PENA1/2](#)

Oxide Inhibiting Electrical Joint Compound, 1/2 OZ, For Al-Al, Al-Cu & Al Conduit Threads.



Application

For Aluminum To Copper, Aluminum To Aluminum, Aluminum To Conduit

General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Container Type	Tube
EU RoHS Indicator	Yes
Pour Point	-15 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
Type	A
UPC	781810592601
UPC 12 Digit	7818105926011
Viscosity at 100 Fahrenheit	305 °F

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Container Size	1/2 oz
Minimum Pack Quantity	50

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_PENA_LineArt](#)
[Sales Drawings - sc211487-01](#)
[SDS - PENETROX A PORTUGUESE SDS \(GHS\) \(2019-07\)](#)
[SDS - PENETROX A GERMAN SDS \(GHS\) \(2019-07\)](#)
[SDS - PENETROX A ESPANOL SDS \(GHS\) \(2019-07\)](#)
[SDS - PENETROX A ESTONIAN SDS \(GHS\) \(2019-07\)](#)
[SDS - PENETROX A SDS \(GHS\) \(2019-07\)](#)
[SDS - PENETROX A FRENCH SDS \(GHS\) \(2019-07\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-PENA1/2-SPEC-EN | REV 5/2024