



# PENAQT, Oxide Inhibitor, Quart Container

By Burndy  
Catalog # [PENAQT](#)

Oxide Inhibiting Electrical Joint Compound, 1 Quart, For Al-Al, Al-Cu & Al Conduit Threads.



## Application

For Aluminum To Copper, Aluminum To Aluminum, Aluminum To Conduit

## General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Container Type	Tub
EU RoHS Indicator	Yes
Pour Point	-15 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
Type	A
UPC	781810592908
UPC 12 Digit	7818105929088
Viscosity at 100 Fahrenheit	305 °F

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Container Size	1 Quart
Minimum Pack Quantity	1

## Product Assets

- [3D Models - PENAQT\\_MODEL-IGES](#)
- [3D Models - PENAQT\\_MODEL-PDF](#)
- [3D Models - PENAQT\\_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Sales Drawings - 50001188](#)
- [SDS - PENETROX A ESPANOL SDS \(GHS\) \(2019-07\)](#)
- [SDS - PENETROX A GERMAN SDS \(GHS\) \(2019-07\)](#)
- [SDS - PENETROX A FRENCH SDS \(GHS\) \(2019-07\)](#)
- [SDS - PENETROX A ESTONIAN SDS \(GHS\) \(2019-07\)](#)
- [SDS - PENETROX A SDS \(GHS\) \(2019-07\)](#)
- [SDS - PENETROX A PORTUGUESE SDS \(GHS\) \(2019-07\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-PENAQT-SPEC-EN | REV 1/2024