


Nylon Splice For 16 - 14 AWG

By Burndy
Catalog # SN14



Copper Butt Splice, 16-14 AWG, 1.25" Splice Length, Nylon Insulated, Tin Plated, 600 Volts Max.

Features

- Seamless tubing, high quality design without seams to split
- Electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Tin plating provides durable long-lasting resistance to corrosion
- Positive center wire stop for proper depth of wire insertion
- Nylon is locked into position

Application

For Heavy Duty Application Requirements

General

Color Code	Blue
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Unplated
Sub Brand	INSULINK
Temperature Rating	105
Trade Name	INSULINK™
Type	SN
UPC	781810736982
UPC 12 Digit	7818107369822

Dimensions

Cable Insulation Diameter Maximum	0.15 in
Dimension - Diameter Max Size inch	0.15 in
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.25 in
Dimension - Outside Diameter inch	0.15 in
Dimension - Strip Length inch	3/16 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 - 14 AWG
Conductor Size	16 - 14 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_SN10_LineArt](#)
[Sales Drawings - 50094191](#)



A proud member of the Hubbell Family.