


SNM14, Nylon Splice For 16 - 14 AWG

By Burndy
Catalog # [SNM14](#)



Nylon Splice For 16 - 14 AWG.

Application

The type SNM INSULINK is a high quality nylon insulated butt splice designed to meet military MS25181, class 1 requirements.

General

Catalog Number	SNM14
Color Code	Blue
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	INSULINK
Temperature Rating	105
Trade Name	INSULINK™
Type	SNM
UPC	781810736555
UPC 12 Digit	7818107365555

Dimensions

Cable Insulation Diameter	0.15 in
Maximum	
Dimension - Diameter Max Size	0.15 in
inch	
Dimension - L Length Overall	39 mm
mm	
Dimension - Length Overall	1.53 in
inch	
Dimension - Outside Diameter	0.15 in
inch	
Dimension - Strip Length inch	7/32 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size	16 - 14 AWG
Range	
Conductor Size	16 - 14 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_SNM14_LineArt](#)
[Sales Drawings - 50094192](#)
[Specifications - SNM14](#)