



## Q2A314N, Two Conductor Four Hole Mounting Heavy Duty Copper Lug Connector, 250-350 kcmil, 1/2" Stud, 1-3/4" Spacing, 2 Screws

By Burndy  
Catalog # [Q2A314N](#)



Copper Terminal, 2 Hole, 250-350 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, 2 Screws.

### Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

### General

Catalog Number	Q2A314N
Connector Type	Duel Clamp
Installation Torque	325 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	4
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810321805
UPC 12 Digit	7818103218055

### Dimensions

Dimension - B Length inch	1.19 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.09 in
Dimension - F Width Center to Center inch	0.75 in
Dimension - Height fraction	1-11/16 in
Dimension - Height inch	1.69 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	114 mm
Dimension - Length Overall inch	4.44 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	3.00 in
Dimension - Stud Size inch	1/2
Dimension - Width inch	3.00 in

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil
Conductor - Copper Str Size Range	250 kcmil-350 kcmil
Conductor Size	250-350 kcmil
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity 2

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_Q2A284N\\_LineArt](#)  
[Sales Drawings - sd023314-01](#)  
[Specifications - Q2A314N](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-Q2A314N-SPEC-EN | REV 8/2024