



# Vinyl Splice For 16 - 14 AWG

By Burndy  
Catalog # [SP14](#)

Copper Splice, 16-14 AWG, 1" Splice Length, Vinyl Insulated.



### Features

- Manufactured from seamless electrolytic copper tubing to provide maximum conductivity and tensile strength in a high quality design with no seams to split
- Funnel entry for easy wire insertion
- Electro-tin plating provides durable, long lasting resistance to corrosion

### Application

For Accommodating A Broad Range Of 600 Volt Cables

### General

Color Code	Blue
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	VINYLINK
Temperature Rating	105° C
Trade Name	VINYLINK™
Type	SP
UPC	781810712016
UPC 12 Digit	7818107120166

### Dimensions

Cable Insulation Diameter Maximum	0.18 in
Dimension - Diameter Max Size inch	0.18 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in
Dimension - Outside Diameter inch	0.18 in
Dimension - Strip Length inch	1/4 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 - 14 AWG
Conductor Size	16 - 14 AWG

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

### Product Assets

[3D Models - SP14\\_MODEL-IGES](#)  
[3D Models - SP14\\_MODEL-PDF](#)  
[3D Models - SP14\\_MODEL-STEP](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_KTFBS\\_LineArt](#)  
[Sales Drawings - 50094190](#)



