

QA462NTN, Tin Plated Heavy Duty Two Hole Mounting Copper Lug Connector, 1100-1500 kcmil, 1/2" Stud, 1-3/4" Spacing, 1 Screw

By Burndy
Catalog # [QA462NTN](#)



High Cu Alloy Terminal, Heavy Duty, 2-NEMA Holes, 1100 - 1500 kcmil Commercial, 1300 Navy, 1 Screw, Electro-Tin Plated, 0.56" Hole Dia.

Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

General

Connector Type	Single Clamp
Installation Torque Recommended in-lb	600 LBS/in
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810421079

Dimensions

Dimension - D inch	3.00 in
Dimension - Height inch	2.88 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	133 mm
Dimension - Length Overall inch	5.25 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	2.12 in
Dimension - Stud Size inch	1/2
Dimension - Width mm	54 mm
Weight	3.1 lb

Conductor Related

Conductor - Copper Str Navy Size	1300 (127) Navy
Conductor - Copper Str Navy Size Range	1300 (127) Navy
Conductor - Copper Str Size	1250 kcmil;1300 kcmil;1500 kcmil
Conductor - Copper Str Size Range	1100 kcmil-1500 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Navy-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - sa008947](#)

