

# T1012, Uninsulated Ring Terminal For 12 - 10 AWG

By Burndy  
Catalog # T1012



Uninsulated Ring Terminal For 12 - 10 AWG.

## Features

Long neck terminal permits easy bending and stacking of several terminals on a common stud

## Application

For Control Wiring And Other Standard Duty Applications

## General

Catalog Number	T1012
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYDENT
Trade Name	HYDENT™
Type	Ring Tongue
UPC	781810525630
UPC 12 Digit	7818105256300

## Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - L Length Overall mm	31 mm
Dimension - Length Overall inch	1.21 in
Dimension - Pad Width inch	0.69 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Z (inch)	0.61 in

## Conductor Related

Conductor - Copper Solid Size	22
Conductor - Copper Solid Size Range	22
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> </ul>

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Carton Quantity	100
Minimum Pack Quantity	50

## Product Assets

- [3D Models - T1012\\_MODEL-STEP](#)
- [3D Models - T1012\\_MODEL-IGES](#)
- [3D Models - T1012\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094154](#)
- [Specifications - T1012](#)