

# QB342N, Right Angled Two Hole Mounting Heavy Duty Copper Lug Connector, 400-500 kcmil, 5/8" Stud, 1 Screw



By Burndy  
Catalog # [QB342N](#)

Cast Cu Alloy Terminal, 2 Pad Holes, 400 kcmil - 500 kcmil, 4.69 IN L, 1.38 IN W, 5/8-18 IN Bolt.

## Features

- Side Entry terminal
- Joins a range of cable at right angles to terminal blocks
- One-wrench installation

## General

Catalog Number	QB342N
Connector Type	Terminal
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810006054

## Dimensions

Dimension - B Length fraction	1-19/50 in
Dimension - B Length inch	1.38 in
Dimension - D inch	3.25 in
Dimension - Height fraction	49
Dimension - Height inch	1.94
Dimension - Height mm	49.3 mm
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	119 mm
Dimension - Length Overall inch	4.69

Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.38 in

## Conductor Related

Conductor - Copper Str Size	400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	400 kcmil-500 kcmil
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	2088

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_QB\\_LineArt](#)  
[Sales Drawings - sc023473-01](#)  
[Specifications - QB342N](#)