

Twin Clamping Heavy Duty Copper Lug Connector

By Burndy
Catalog # [QQA34](#)



Copper Terminal, Heavy Duty, 1 Hole, 400-500 kcmil, 1/2" Stud, 2 Screws.

Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

General

Connector Type	Duel Clamp
Installation Torque Recommended in-lb	375 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810325803

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.63 in
Dimension - Height fraction	2 in
Dimension - Height inch	2.00 in
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	124 mm
Dimension - Length Overall inch	4.88 in
Dimension - N inch	0.81 in
Dimension - Pad Width inch	1.38 in

Conductor Related

Conductor - Copper Str Navy Size	400 (127) Navy;500 (127) Navy
Conductor - Copper Str Navy Size Range	400 (127) Navy-500 (127) Navy
Conductor - Copper Str Size	400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	400 kcmil-500 kcmil
Conductor Size	400-500 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Navy-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_QQA_LineArt](#)
[Sales Drawings - SA..005911-01](#)

