

# QQA344N, Twin Clamping Four Hole Mounting Heavy Duty Copper Lug Connector



By Burndy  
Catalog # [QQA344N](#)

High Copper Alloy QIKLUG™, 400 - 500kcmil CU, 1/2" Stud.

## Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

## General

Catalog Number	QQA344N
Connector Type	Dual Clamp
Material	Copper
Physical Attribute - Number of Holes	4
Physical Attribute - Number of Screws	2
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810006023
UPC 12 Digit	7818100060233

## Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.06 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	1-15/16 in
Dimension - Height inch	1.94 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	165 mm
Dimension - Length Overall inch	6.50 in

Dimension - N inch	0.62 in
Dimension - Pad Width inch	3.00 in

## Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

## Conductor Related

Conductor - Copper Str Size	400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	400 kcmil-500 kcmil
Conductor Size	400-500 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Str Navy-Size</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_QQA\\_LineArt](#)
- [Specifications - QQA344N](#)